

Models &	<u>Options</u>			
Part #	Description	Part #	Description	
Step 1: Select an	Air Purifier Module (Fan/Filter/Controls) 80 CFM per foot of table	<u>length</u> <u>Optional R</u>	<u>eplacement Hepa Filter</u>	
L-830	COVID-CBF1/700/2-Zone 700 m3/h (400 CFM) FILTER UNIT. HEPA H14(8M2). Vertical Duct D.200/ 1.1m. EC 1-phase, 120V, 60Hz,17		•	filter coronavirus H14 (8M2) for COVID- rtificate and Leak Test.
L-831	COVID-CBF1/700/2-Zone 1000 m3/h (600 CFM) FILTER UNIT. HEP H14(13M2). Vertical Duct D.200/ 0.8m. EC 1-phase, 120V, 60Hz, 1		·	filter coronavirus H14 (13m2) for COVID- ertificate and Leak Test.
Step 2: Select Diff	usion Hood (should be the same length as the table length)			•
L-818	Diffusion Hood 1m (2 Persons) . Inlet D.200, White Hose 0.5m/D.2 Suspension Chains 4x2m and 4+4 Hooks. White.	200,		
L-819	Diffusion Hood 1.5m (4 Persons). Inlet D.200, White Hose 0.5m/D Suspension Chains 4x2m and 4+4 Hooks. White.	2.200,	Air Purifier Modu	ule
L-820	Diffusion Hood 2m (6 Persons). Inlet D.200, White Hose 0.5m/D.2 Suspension Chains 4x2m and 4+4 Hooks. White.	200,		
L-829	Diffusion Hood 2.5m (8 Persons). Inlet D.200, White Hose 0.5m/D Suspension Chains 4x2m and 4+4 Hooks. White.	0.200,		
Step 3: Select Duc	ct Kit (L=Distance from ceneter of table to the unit)		i	
L-824	Horizontal Duct work L=2m. 2 Bends 90/D.200, Duct D.200 (0.8m+0.8m), Suspension Chains 4x2m and 2+2 Hooks. White.			
L-825	Horizontal Duct work L=2.3 m. 2 Bends 90/D.200, Duct D.200(1.1m+0.8m), Suspension Chains 4x2m and 2+2 Hooks. Wh	nite.		
L-826	Horizontal Duct work L=2.6m. 2 Bends 90/D.200, Duct D.200 (1.1m+1.1m), Suspension Chains 4x2m and 2+2 Hooks. White			
L-827	Horizontal Duct work L=2.8m. 2 Bends 90/200, Duct D.200 (0.8m+0.8m+0.8m), Suspension Chains 6x2m and 6+6 Hooks. W	hite.		
Step 4: Select Hor	izontal Extension Duct (ONLY required for L great than 2.8m)			
L-836	Horizontal Extension Duct L=0.6m /D.200, Male Coupling D.200, Suspension Chains 2x2m and 2+2 Hooks. White.			
L-837	Horizontal Extension Duct L=0.8m /D.200, Male Coupling D.200, Suspension Chains 2x2m and 2+2 Hooks. White.	Diffus	sion Hood	
L-838	Horizontal Extension Duct L=1.1m /D.200, Male Coupling D.200, Suspension Chains 2x2m, 2+2 Hooks. White.			
CUSTOMER:		The device depicted and described hereon embodies proprietary information owned by	Drawn By: Mark Fanous	, ,
CUSTOMER PO: PROJECT:		the manufacturer. All Design, manufacturing,	Date: 2/4/2021 Scale: NTS	WITH H14 FILTRATION
ENGINEER:	SUIENGE	reproduction, sales and patent rights regarding this device or drawing reserved except where	Weight: N/A	
SALES REP: TAGGING:		explicit right is guaranteed in writing. We reserve the right to make design changes.	Copyright C 2021 by Lev-Co, The Local Exhaust and Ventilation Company Inc. All rights reserved. No part of this product may be reproduced or used in any manner without written permission of the copyright owner.	Drawing No: Sheet: 2 / 4 File Name: (20-011) ICA OVER TABLE HOOD WITH H14 FILTRATION
	VEHICLE EXHAUST • FUME EXTRACTION • OIL MIST	FILTRATION • DUST BOOTHS		WWW.LEV-CO.COM

AIR PURIFIER MODULE SOUND LEVEL AND ACH

SOUND LEVELS

ICA-700 (400 CFM)

400 CFM	CFM	dB/A
700	420	59
400	240	53
300	180	49
200	120	44
150	90	39

ICA-1000 (600 CFM)

600 CFM	CFM	dB/A
950	570	66
700	420	63
450	270	57
300	180	49
250	150	46
200	120	43

ACH - AIR CHANGES PER HOUR

	ROOM AREA (ff^2)	ROOM VOLUME (ff^3) (8' CEILING HEIGHT)	CADR (CFM)	ACH WITHOUT K FACTOR	ACH WHEN ALLOWING FOR A K FACTOR OF 1.5
400 CFM	900	9000	400	2.7	1.8
600 CFM	900	9000	600	4.0	2.7

NB: CADR W/O DUCT, PERFORMANCE WILL BE LESS ONCE YOU ALLOW FOR FRICTION LOSSES IN THE DUCT CADR = CLEAN AIR DELIVERY RATE ACH = AIR CHANGES PER HOUR



The device depicted and described hereon embodies proprietary information owned by the manufacturer. All Design, manufacturing, reproduction, sales and patent rights regarding this device or drawing reserved except where explicit right is guaranteed in writing. We reserve the right to make design changes.

	Drawn By:	Mark Fanous
	Date:	2/4/2021
_	Scale:	NTS
y	Weight:	N/A

Copyright © 2021 by Lev-Co. The Local Exhaust and Ventilation
Company Inc. All rights reserved. No part of this product may be reproduced or used in any


(20-011) ICA "OVER TABLE HOOD" WITH H14 FILTRATION


SPECIFICATION DRAWING

Drawing No: | Sheet: 3 / 4 | File Name: (20-011) ICA OVER TABLE HOOD WITH HI4 FILTRATION

Customer Dimensioning Template

Feel free to us ethis template to fill out all the dimensioning information of the room you are looking to install this unit in.





CUSTOMER: **CUSTOMER PO:** PROJECT: ENGINEER: SALES REP: TAGGING:

The device depicted and described hereon embodies proprietary information owned by the manufacturer. All Design, manufacturing, reproduction, sales and patent rights regarding Weight: this device or drawing reserved except where explicit right is guaranteed in writing. We reserve the right to make design changes.

Mark Fanous Drawn By: Date: 2/4/2021 Scale: NTS N/A

Copyright C 2021 by Lev-Co, The Local Exhaust and Ventilation

(20-011) ICA "OVER TABLE **HOOD" WITH H14 FILTRATION**

SPECIFICATION DRAWING

Drawing No:

Sheet: 4 / 4 File Name: (20-011) ICA OVER TABLE HOOD WITH H14 FILTRATION